



[See all 4 Products in Family](#)

Richardson Gratings™ 79 Grooves, 25 x 50mm, 63° Blaze Angle, Echelle Grating

See More by [Richardson Gratings™](#)



Stock #15-742 **6 In Stock**

1 MRP ₹31,781

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹31,781 each
Qty 10-24	₹28,602 each
Need More?	Request Quote

Product Downloads

General

Echelle Grating **Type:**

401E **Master Reference:**

Physical & Mechanical Properties

25.0 x 50.0 ±0.1	Dimensions (mm):
>90	Clear Aperture (%):
Ruled Grating	Construction:
50.00	Length (mm):
6.00 ±0.5	Thickness (mm):
25.00	Width (mm):
±1	Centering of Ruled Area on Substrate (mm):
±0.15	Alignment of Grooves to Edge (°):
<0.05	Groove Spacing Tolerance (%):

Optical Properties

79	Groove Density (grooves/mm):
All	Blaze Wavelength (nm):
63	Blaze Angle (°):
Aluminium	Coating:
Float Glass	Substrate: □
M4	Reflected Wavefront, RMS:
Unpolarized	Polarization:
1	Spectral Order (m):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Highest Resolving Power and Dispersion
- Low Groove Density for Use in Higher Orders
- Groove Spacing Tolerance <0.05%
- Custom Sizes Available

Richardson Gratings™ Echelle Reflective Diffraction Gratings feature superior resolving power and dispersion compared to other reflective diffraction gratings. These gratings are characterized by coarse groove spacings, relatively low groove densities and high blaze angles. They are suitable for use from near-UV wavelengths to the infrared (~20µm). Richardson Gratings™ Echelle Reflective Diffraction Gratings are ideal for applications such as compact high resolution spectrometers with high angular dispersion and throughput. Custom sizes are available on request.

Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;