

780nm Dual Stage Free-Space Optical Isolator



780nm Dual Stage Free-Space Optical Isolator, #35-983

Stock **#35-983** 3 In Stock

-

1

+

₹3,44,619

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,44,619 each
Need More?	Request Quote

Product Downloads

General	
Dual Stage Optical Isolator	Type:
Faraday	Style:

Physical & Mechanical Properties	
4.7	Clear Aperture CA (mm):

Optical Properties

80	Minimum Transmission (%):
90 (typical)	Transmission (%):
780	Design Wavelength DWL (nm):
760 - 805	Wavelength Range (nm):
40 W, 4 kW/cm ² @ DWL	Damage Threshold, By Design: ☐
67	Typical Isolation at Design Wavelength (dB):
60	Minimum Isolation at Design Wavelength (dB):
40 W, 4 kW/cm ² @ DWL	Damage Threshold, CW:

Environmental & Durability Factors

+15 to +40	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE