

TECHSPEC® 7X, NIR Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock #39-745 10 TO 12 DAYS



1



₹41,969.00

ADD TO CART

Qty 1-9

₹41,969.00

Qty 10+

₹37,114.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser NIR (1030-1550nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm): 7.1
Exit Aperture (mm): 25.5
Expansion Power: 7X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 92.16
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >95.8 (nominal)
Type: Beam Expander
Weight (g): 169
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: λ/10 for 3.6mm input beam (nominal, λ = DWL)
Coating Specification: R _{avg} ≤ 0.7% @ 1030 - 1550nm @ 0° AOI
Wavelength Range (nm): 1030 - 1550
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 2 J/cm² @ 1064nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View