

8" Length, 1/4-20 and 1/4-20, Steel Post



Stock **#72-798** NEW **16 In Stock**

-

1

+

₹861

ADD TO CART

Volume Pricing	
Qty 1+	₹861 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

English

Type:

Physical & Mechanical Properties

12.7

Diameter (mm):

0.5	Diameter (inches):
203.2	Length (mm):
8	Length (inches):

Threading & Mounting

Thread 1: 1/4 - 20 Thread 2: 1/4 - 20	Male Thread:
--	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/1/4-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

Note: All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" keysize, or other tools to rotate the post easily.