


[See all 3 Products in Family](#)

**TECHSPEC® 50.8mm Dia. Uncoated, Silicon, Laser Mirror**



Stock #90-140 **NEW** 1 In Stock

- 1 + MRP ₹19,876

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹19,876 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror Substrate **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Commercial Polish **Back Surface:**

50.80 +0.00/-0.10	<b>Diameter (mm):</b>
9.53 ±0.10	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
40-20	<b>Surface Quality:</b>
N/A	<b>Coating Specification:</b>
λ/10	<b>Surface Flatness (P-V):</b>
Uncoated	<b>Coating:</b>
Optical Grade Silicon	<b>Substrate:</b> <input type="checkbox"/>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Vietnam	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Silicon Substrate for Thermally Demanding Ultrafast Setups
- λ/10 Surface Flatness and 40-20 Surface Quality
- Available In Standard Diameters for Coating Flexibility and System Integration

TECHSPEC® Silicon Laser Mirror Substrates feature a high-thermal-conductivity silicon substrate designed for thermally demanding high-power and ultrafast laser applications. Optimized for efficient heat distribution in challenging optical setups, these substrates help mitigate thermally induced wavefront distortion. Designed as a coating-ready platform, TECHSPEC® Silicon Laser Mirror Substrates provide a flexible foundation for custom broadband or low-dispersion mirror solutions. Available in 12.7mm, 25.4mm, and 50.8mm diameters, these mirrors offer flexibility for integration into a wide range of laser system configurations.