

**TECHSPEC® 800-1150nm, 20mm Diameter Ultrafast-Enhanced Silver Coated,  $\lambda/10$  Mirror**



Stock #22-014 **2 In Stock**

⊖ 1 ⊕ MRP ₹12,612

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹12,612 each
Qty 6-25	₹10,089 each
Qty 26-49	₹9,484 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

20.00 +0.00/-0.20 **Diameter (mm):**

3.00 ±0.20 **Thickness (mm):**

Commercial Polish	<b>Back Surface:</b>
Protective as needed	<b>Bevel:</b>
90	<b>Clear Aperture (%):</b>
+0.00/-0.20	<b>Dimensional Tolerance (mm):</b>
Ground	<b>Edges:</b>
30	<b>Parallelism (arcsec):</b>

## Optical Properties

0.80 - 1.15	<b>Wavelength Range (µm):</b>
Ultrafast-Enhanced Silver	<b>Coating Type:</b>
Ultrafast-Enhanced Silver (800-1150nm)	<b>Coating:</b>
M10	<b>Surface Flatness (P-V):</b>
800 - 1150	<b>Wavelength Range (nm):</b>
<b>Fused Silica</b> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
R <sub>avg</sub> >99% @ 850 - 1150nm, 0° R <sub>s</sub> >99% @ 800 - 1150nm, 45° R <sub>p</sub> >98.5% @ ~850 - 1100nm, 45°	<b>Coating Specification:</b>
20-10	<b>Surface Quality:</b>
0.35 J/cm <sup>2</sup> @ 1030nm, 200fs, 1 pulse (typical) 0.10 J/cm <sup>2</sup> @ 1030nm, 200fs, 100Hz, 1000 pulses (typical)	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>
0 ±30fs <sup>2</sup> @ 800 - 1150nm	<b>GDD Specification:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

TECHSPEC® M10 First Surface Mirrors are ideal for demanding beam steering and reflection applications in the visible and IR spectra. With a precision fused silica substrate, the mirrors feature a low coefficient of thermal expansion while being highly durable and resistant to abrasion. These precision mirrors are available in a variety of sizes and coating options, including enhanced aluminum, protected gold, and protected silver. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact to the performance on the metal coating. TECHSPEC® M10 First Surface Mirrors can be utilized in various optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

**Note:** Surface flatness is measured before coating.

## Technical Information



800-1150nm Ultrafast-Enhanced Silver

## Compatible Mounts

;