

TECHSPEC[®] 800-1150nm, 35mm Diameter Ultrafast-Enhanced Silver Coated, λ /10 Mirror



Stock #22-018 4 In Stock

-

1

+

₹13,235

ADD TO CART

Volume Pricing	
Qty 1-5	₹13,235 each
Qty 6-25	₹10,588 each
Qty 26-49	₹9,926 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

35.00 +0.00/-0.20

Diameter (mm):

Commercial Polish

Back Surface:

Dimensional Tolerance (mm):	
+0.00/-0.20	
Bevel:	
Protective as needed	
Clear Aperture (%):	
90	
Edges:	
Ground	
Parallelism (arcsec):	
30	
Thickness (mm):	
5.00 ±0.20	

Optical Properties

Surface Flatness (P-V):	
λ/10	
Substrate: 	
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Coating Specification:	
R _{avg} >99% @ 850 - 1150nm, 0°	
R _s >99% @ 800 - 1150nm, 45°	
R _p >98.5% @ ~850 - 1100nm, 45°	
Coating:	
Ultrafast-Enhanced Silver (800-1150nm)	
Coating Type:	
Ultrafast-Enhanced Silver	
Wavelength Range (μm):	
0.80 - 1.15	
Wavelength Range (nm):	
800 - 1150	
GDD Specification:	
0 ±30fs ² @ 800 - 1150nm	
Damage Threshold, Reference: 	
0.35 J/cm ² @ 1030nm, 200fs, 1 pulse (typical)	
0.10 J/cm ² @ 1030nm, 200fs, 100Hz, 1000 pulses (typical)	

Regulatory Compliance

Certificate of Conformance:	
View	
Country of Origin:	
United States	
Imported By:	
Edmund Optics India Private Limited	


Product Details

- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

TECHSPEC® λ/10 First Surface Mirrors are ideal for demanding beam steering and reflection applications in the visible and IR spectra. With a precision fused silica substrate, the mirrors feature a low coefficient of thermal expansion while being highly durable and resistant to abrasion. These precision mirrors are available in a variety of sizes and coating options, including enhanced aluminum, protected gold, and protected silver. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact to the performance on the metal coating. TECHSPEC® λ/10 First Surface Mirrors can be utilized in various optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Note: Surface flatness is measured before coating.

Technical Information



800-1150nm Ultrafast-Enhanced Silver

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts