


[See all 8 Products in Family](#)

## 80 Grooves/mm, 12.7mm Sq, Transmission Grating Beamsplitter



Stock #46-069 **10 In Stock**

MRP ₹15,134

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹15,134 each
Qty 10-24	₹13,621 each
Qty 25+	₹11,350 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Transmission Diffraction Grating **Type:**

#### Physical & Mechanical Properties

12.7 x 12.7 ±0.5 **Dimensions (mm):**

90 **Clear Aperture (%):**

Blazed Grating	<b>Construction:</b>
12.70	<b>Length (mm):</b>
3.00 ±0.5	<b>Thickness (mm):</b>
12.70	<b>Width (mm):</b>

### Optical Properties

80	<b>Groove Density (grooves/mm):</b>
632.8	<b>Design Wavelength DWL (nm):</b>
<a href="#">B270</a>	<b>Substrate:</b> <input type="checkbox"/>

### Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
<b>Imported By:</b> Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	


### Product Details

- Ideal for Laser Beam Division
- Designed for 0 Degree AOI
- Low Groove Density for Maximized Beam Separation

Transmission Grating Beamsplitters are commonly used for laser beam division and multiple laser line separation in visible wavelengths. The transmitted beam is diffracted into multiple orders. Edmund Optics' transmission grating beamsplitters consist of an index-matched epoxy replica on a polished glass substrate for a high total efficiency. Transmission Grating Beamsplitters are available in several gratings, offering different dispersion and power distributions. The diffraction angle for any wavelength may be calculated using the grating equation for normal incident light.

**Handling Gratings:** Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

### Technical Information



He-Ne Diffracted Order Typical Distribution @ 632nm (%)					Stock No.	
2	-1	0	+1	+2	12.7mm x 12.7mm	25mm x 25mm
—	—	41	32	—	<a href="#">#46-067</a>	<a href="#">#46-068</a>
5	25	25	25	5	<a href="#">#46-069</a>	<a href="#">#46-070</a>
—	20	45	20	—	<a href="#">#46-071</a>	<a href="#">#46-072</a>
—	25	28	25	—	<a href="#">#46-073</a>	<a href="#">#46-074</a>

### Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support

team.



Component Handling Tools

## Compatible Mounts

---

;