

[See all 8 Products in Family](#)

203.2mm/8.0" Optic Dia., Optical Cell Kinematic Mount



Stock #36-476 [CONTACT US](#)

- 1 + ₹2,18,216

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | ₹2,18,216 each |
| Qty 5-9 | ₹1,92,551 each |
| Qty 10-25 | ₹1,77,184 each |
| Need More? | Request Quote |

Product Downloads

General

Adjustable - Tip-Tilt **Type:**

Circular **Type of Optics:**

5° **Range:**

8.06 Inner Diameter (inches):

Optic Holding Style:
Three Spring-Loaded Clips

Physical & Mechanical Properties

7.62 Clear Aperture CA (inches):

193.5 Clear Aperture CA (mm):

158.8 Optical Centerline (mm):

12.00 x 6.00 x 11.50 Dimensions (inches):

304.8 x 152.4 x 292.1 Dimensions (mm):

27.0 Weight (lbs):

Construction:
Black Anodized Aluminum, Stainless Steel

8.00 Diameter of Compatible Optics (inches):

6.25 Optical Centerline (inches):

39.5 Max. Thickness of Compatible Optics (mm):

0.031 Adjustment Screw Pitch (inches):

Threading & Mounting

203.2 Size of Compatible Optics (mm):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Product Details

- Robust Kinematic Mounts for Larger Diameter Optics
- Ball Pivot and Fine Pitch Screws Provide Pitch and Roll
- 50% Greater Resolution than Micrometer Adjustments


Optical Cell Kinematic Mounts provide highly stable kinematic movement with two axis tilt (pitch and roll) provided by a precise ball pivot adjustment and an orthogonal three-point suspension. Adjustment is made by three 64-pitch screws (two 64-pitch screws for 1-2" diameter model). For the 6" diameter model, adjustment is made by two 64-pitch screws for and with three 32-pitch screws for 8" up to 12.5" diameter models. Optical Cell Kinematic Mounts feature fine pitch screws, which permit 50% greater resolution than a micrometer. An angled base on the mount allows for stand-alone installation and mounting. These mounts have integral optic cell design allowing optics to be held undistorted.

Note: For mounting 12" diameter optics in our 12.5" Diameter Optical Mount, use the 12.5" to 12" Adapter Kit (#12-226). The Adapter Kit and 12.5" Diameter Optical Mount are offered together as #12-227.

Technical Information


| Optic Diameter | A | B | C | D | E | F | G | H | I | J | K | Stock No. |
|----------------|--------------|------|------|------|------|------|------|------|---|------|---|-------------------------|
| 1-2" | 2.25-20 TPI | 3.75 | 2.00 | 2.00 | 0.38 | 2.00 | 3.50 | 0.28 | - | 2.12 | - | #53-964 |
| 3" | 3.25-20 TPI | 5.75 | 3.00 | 4.00 | 1.25 | 3.38 | 6.25 | 0.28 | - | 5.00 | - | #53-965 |
| 4.25" | 4.625-20 TPI | 5.75 | 3.00 | 4.00 | 1.25 | 3.38 | 6.25 | 0.28 | - | 5.00 | - | #57-872 |

1" - 4.25" Angled Optical Cell Mounts



Units: inches


4.25" Straight Optical Cell Mount



Units: inches

| Optic Diameter | A | B | C | D | E | F | G | H | I | J | K | Stock No. |
|----------------|--------------|-------|------|-------|------|------|-------|------|-------|-------|------|-------------------------|
| 6" | 6.187-32 TPI | 8.00 | 6.00 | 5.00 | 5.00 | 4.50 | 8.00 | 0.28 | 5.75 | 6.00 | 1.19 | #36-474 |
| 8" | 8.06 | 12.00 | 7.00 | 10.00 | 6.00 | 6.25 | 11.50 | 0.28 | 7.62 | 9.00 | 1.60 | #36-476 |
| 10" | 10.06 | 16.00 | 8.00 | 12.00 | 6.00 | 8.00 | 15.00 | 0.53 | 9.58 | 12.50 | 1.75 | #36-478 |
| 12.5" | 12.56 | 16.00 | 8.00 | 12.00 | 6.00 | 8.00 | 15.00 | 0.53 | 12.08 | 12.50 | 2.13 | #36-480 |

8" - 12.5" Angled Optical Cell Mounts



Units: inches