

800nm, 12.5mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-218** 20+ In Stock

-

1

+

₹6,539

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,539 each
Qty 10-25	₹5,878 each
Qty 26-49	₹5,566 each
Need More?	Request Quote

Product Downloads

General	
Longpass Filter	Type:
Physical & Mechanical Properties	
12.50 +0.00/-0.20	Diameter (mm):
2.00 ±0.10	Thickness (mm):


90	Clear Aperture (%):
ML-C-48497A, Section 3.4.1	Physical Durability:
Optical Properties	
0	Angle of Incidence (°):
≥2.0	Optical Density OD (Average):
800.00 ±16	Cut-On Wavelength (nm):
BOROFLOAT®	Substrate: 
Hard Coated	Coating:
500 - 765	Rejection Wavelength (nm):
60-40	Surface Quality:
≥85	Transmission (%):
840 - 1600	Transmission Wavelength (nm):
500 - 1600	Wavelength Range (nm):

Environmental & Durability Factors	
ML-STD-810F, Section 507.4	Environmental Durability:
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Sharp Cut-On Wavelength
 - ≥85% Transmission and OD 2.0 Blocking
 - 6mm Square or 12.5/25mm Diameter Sizes
 - [TECHSPEC® OD 4.0 Longpass Filters](#) Also Available
- OD 2.0 Longpass Filters are cost-effective filters with cut-on wavelengths ranging from 400 to 950nm. These longpass filters provide ≥85% transmission across a transmission band that extends out to 1600nm while providing OD 2.0 blocking across their rejection band. The back surface of each filter is coated with an antireflection (AR) coating, increasing the overall efficiency of the filter. OD 2.0 Longpass Filters can be combined with OD 2.0 Shortpass Filters to create custom bandpass filters to meet application requirements in the visible or near-infrared. These longpass filters are ideal for use in fluorescence applications or separating spectral orders, with the 6 x 6mm sized filters suitable for integration into optical instrumentation requiring cost-effective, lightweight filters.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts