


TECHSPEC®

800nm, 25.2 x 35.6mm High Performance Fluorescence Dichroic Filter



Stock #34-747 **2 In Stock**

1 MRP ₹52,161

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹52,161 each
Qty 6-25	₹44,291 each
Qty 26-49	₹41,163 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	Download All

General

Type: Dichroic Filter

Physical & Mechanical Properties

Dimensions (mm):	25.2 x 35.6	Length (mm):	35.60
Thickness (mm):	1.05 ±0.1	Width (mm):	25.20
Dimensional Tolerance (mm):	+0.0/-0.2	Physical Durability:	Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2

Optical Properties

Angle of Incidence (°):	45	Cut-On Wavelength (nm):	800.00
Substrate: Fused Silica (Corning 7980)		Coating:	Hard Coated
Reflection (%):	R _{avg} >98%	Reflection Wavelength (nm):	600 - 760
Surface Quality:	40-20	Transmission (%):	T _{avg} >90%
Transmission Wavelength	807 - 1000	Transmitted Wavefront,	λ/10

(nm):		RMS:	
Wavelength Range (nm):	600 - 1000	Surface Flatness (P-V):	$\lambda/2$
Environmental & Durability Factors			
Environmental Durability:	Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7		
Regulatory Compliance			
RoHS 2015:	Compliant	Certificate of Conformance:	View
Reach 247:	Compliant		
Country of Origin:	United States	Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Improved Flatness, Transmitted Wavefront, and Surface Quality
- Ideal for Fluorescence Microscopy or High Magnification Imaging Applications
- Most Popular Cut-On Wavelengths of Fluorescence and Longpass Dichroic Filters
- Standard **Fluorescence Dichroic Filters** are also available

Our TECHSPEC® High Performance Fluorescence Dichroic Filters feature the same broad, flat transmission and reflection ranges as our popular TECHSPEC® Fluorescence Dichroic Filters, but have improved physical parameters. Special attention to surface flatness, transmitted wavefront, and surface quality have resulted in our highest level of precision yet on a filter. These rectangular filters fit into most common Nikon, Zeiss, and Olympus fluorescence microscopes. High Performance Fluorescence Dichroic Filters are a perfect complement to our TECHSPEC® Fluorescence Bandpass Filters. For specific wavelength or size requirements, numerous custom options are available.

The TECHSPEC® Dichroic Filters (sometimes referred to as dichroic plate beamsplitters or dichroic mirrors) feature broad, flat transmission and reflection ranges with an ultra-steep slope between them. These attributes make them ideal for fluorescence imaging or spectral sorting applications, including DNA sequencing and polymerase chain reaction (PCR) diagnostic instruments.

Note: The filter should be oriented in such a way that the incoming light is incident on the surface that the chevron on the edge of the filter points towards (the dielectrically coated surface).

Technical Information


Filter Type	Transmitted Wavefront (RMS)	Surface Quality	Surface Flatness (P-V)	R(avg)	T(avg)
HP Dichroic	$\lambda/10$	40-20	$\lambda/2$	>98%	>90%
Fluorescence Dichroics	1λ	60-40	-	>98%	>90%
Dichroic Longpass	$\lambda/4$	40-20	-	>97%	>85%

Frequently Purchased Together




#67-714 - 16mm C VIS-NIR Series Fixed Focal Length Lens
₹32,922

Qty




#34-725 - 409nm, 25.2 x 35.6mm High Performance Fluorescence Dichroic Filter
₹52,161

Qty



#34-749 - 850nm, 25.2 x 35.6mm High Performance Fluorescence Dichroic Filter
₹52,161

Qty



#60-068 - #40, 27" x 36", 2 Sheets, Non-Adhesive Flock Paper
₹3,239

Qty

Resources

Media Type

- Application Note
- Video
- Published Article
- FAQ
- Glossary
- Trending in Optics

APPLICATION NOTE

The Importance of Optical Filter Orientation...

APPLICATION NOTE

Custom Bandpass Filter using Shortpass an...

VIDEO

Optical Filters Review

VIDEO

Optical Filter Coatings: Comparison of Traditional a...

PUBLISHED ARTICLE

Selecting Color Filter Glass for Life Science Applications

FAQ

What type of material should I look for in a filter?

[View More](#)

