


[See all 25 Products in Family](#)

## 835nm Single Stage Free-Space Optical Isolator



Stock #35-974 [CONTACT US](#)

- 1 + MRP ₹4,76,201

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹4,76,201 each
Qty 5+	₹4,28,783 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Single Stage Optical Isolator **Type:**

Faraday **Style:**

#### Physical & Mechanical Properties

4.7 **Clear Aperture CA (mm):**

## Optical Properties

**Minimum Transmission (%):**

>85

**Transmission (%):**

92

**Design Wavelength DWL (nm):**

835

**Wavelength Range (nm):**

810 - 860

**Damage Threshold, By Design:**

40 W, 4 kW/cm<sup>2</sup> @ DWL

**Typical Isolation at Design Wavelength (dB):**

43

**Minimum Isolation at Design Wavelength (dB):**

>35

## Environmental & Durability Factors

**Operating Temperature (°C):**

+15 to +40

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)