

[See all 5 Products in Family](#)

TECHSPEC[®] 8mm Focal Length, UAV Series Fixed Focal Length Lens



8mm Focal Length, UAV Series Fixed Focal Length Lens



Stock **#22-834** [CONTACT US](#)

-

1

+

MRP ₹82,376

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹82,376 each
Need More?	Request Quote

Product Downloads

General	
UAV Series	Product Family:
Fixed Focal Length Lens	Type:
Infinite Conjugate	Imaging Lens Type:

Physical & Mechanical Properties

Variable	Iris Option:
73.67	Length (mm):
55.00	Maximum Diameter (mm):
55.00	Outer Diameter (mm):
175	Weight (g):
7.17	Maximum Rear Protrusion (mm):
66.68	Maximum Length (mm):
66.50	Minimum Length (mm):

Optical Properties

85.8°	Horizontal Field of View @ Max Sensor Format:
85.8°	Horizontal Field of View, 1.2" Sensor:
81.0°	Horizontal Field of View, 1.1" Sensor:
75.2°	Horizontal Field of View, 1" Sensor:
55.8°	Horizontal Field of View, 2/3" Sensor:
46.8°	Horizontal Field of View, 1/1.8" Sensor:
19.30	Maximum Image Circle (mm):
0.000285	Numerical Aperture NA, Object Side:
12 (9)	Number of Elements (Groups):
425 - 675	Wavelength Range (nm):
8.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
FOV @ Max Sensor Format, H x V (mm): Horizontal: 85.8° Vertical: 74.0° Diagonal: 113.4°	
2.8 - 16	Aperture (f/#):
425 - 675 BBAR	Coating:
425 - 675 BBAR	Coating Specification:
21.362	Entrance Pupil Position (mm):
28.07	Object Space Principal Plane (mm):
-8.41	Image Space Principal Plane (mm):
6.7	Maximum Distortion (%):
-43.257	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1.2"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

N/a	Filter Thread:

N/a	Front Thread:
C-Mount	Mount:
Environmental & Durability Factors	
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team	
Regulatory Compliance	
View	Certificate of Conformance:
China	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	


Product Details

- Compact, Infinite Conjugate Lens Ideal for Photogrammetry
- 8mm, 12mm, 16mm, 25mm, and 35mm Focal Lengths
- 1.2", C-Mbunt Lens
- Up to 24.4 MegaPixels, 2.7µm Pixel Size Sensors


TECHSPEC® UAV Series Fixed Focal Length Lenses are compact, lightweight infinite conjugate lenses designed for the 4th Generation Sony Pregius 1.2" IMX530 and IMX540 sensors for mounting on autonomous vehicles and drones. These lenses are designed with a low Ground Separation Distance (GSD) to enable accurate survey results, and are available in 8mm, 12mm, 16mm, 25mm, and 35mm focal length options. The f/2.8 aperture provide increased light throughput and high-resolution performance. TECHSPEC® UAV Series Fixed Focal Length Lenses are C-Mbunt and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard [optical filters](#). These lenses are ideal for Drone Mapping and Surveying, Aerial Imaging, and Photogrammetry applications.

Note: Call for OEM Quantity and Pricing


Technical Information



#22-834 - 8mm Focal Length, UAV Series Fixed Focal Length Lens, Distortion Plot



#22-834 - 8mm Focal Length, UAV Series Fixed Focal Length Lens, Relative Illumination Plot



#22-834 - 8mm Focal Length, UAV Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, Infinity Working Distance, f2.8