


TECHSPEC® 900nm, 25.2 x 35.6mm, Low GDD Dichroic Shortpass Ultrafast Filter



TECHSPEC® Low GDD Dichroic Shortpass Ultrafast Filters

Stock #14-017 **1 In Stock**

MRP ₹23,003

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹23,003 each
Qty 6-25	₹18,362 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter **Type:**

Physical & Mechanical Properties

25.2 x 35.6 **Dimensions (mm):**

35.60 **Length (mm):**

1.05 ±0.1	Thickness (mm):
25.20	Width (mm):
<hr/>	
+0.0/-0.2	Dimensional Tolerance (mm):
<hr/>	
Optical Properties	
45	Angle of Incidence (°):
900.00	Cut-Off Wavelength (nm):
<hr/>	
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
Hard Coated	Coating:
<hr/>	
>80	P-Polarization Transmission (%):
>97 Average Polarization	Reflection (%):
<hr/>	
960 - 1170	Reflection Wavelength (nm):
>80	S-Polarization Transmission (%):
<hr/>	
60-40	Surface Quality:
>85 Average Polarization	Transmission (%):
<hr/>	
465 - 865	Transmission Wavelength (nm):
λ/4	Transmitted Wavefront, RMS:
<hr/>	
3.00	Slope Factor (%):
±2	Cut-Off Tolerance (%):
<hr/>	
>95	S-Polarization Reflection (%):
>95	P-Polarization Reflection (%):
<hr/>	
Coating Specification: Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated	
465 - 1170	Wavelength Range (nm):
<hr/>	
GDD Specification (Transmission): 80 ±30fs ² @ 610 - 865nm 120 ±80fs ² @ 465 - 865nm	

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
<hr/>	
Compliant	Reach 235:
<hr/>	
United States	Country of Origin:
<hr/>	
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

- Scalable production—from prototype to volume
Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reduced Thickness for Limited GDD
- Broad Transmission and Reflection Ranges
- Ideal for Ultrafast Laser Applications
- Controlled GDD Specification Using [In-House Metrology](#)

TECHSPEC® Low GDD Dichroic Shortpass Ultrafast Filters feature thin substrates and a low group delay dispersion (GDD) coating, making them ideal for use with ultrafast laser sources. Designed for a 45° angle of incidence and covering a range of wavelengths, these spectral filters can be used with Ti:sapphire, Nd:doped, and Yb:doped fiber or glass lasers, as well as with optical parametric oscillators and amplifiers. TECHSPEC Low GDD Dichroic Shortpass Ultrafast Filters are ideal for ultrafast laser applications including multi-photon microscopy, nonlinear fluorescence, and femtosecond stimulated Raman spectroscopy. Please contact us if your application requires an ultrafast optical filter with a custom size or wavelength range.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Compatible Mounts
