

[See all 243 Products in Family](#)

TECHSPEC<sup>®</sup> 9.0mm Dia. x 36.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-121** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

₹2,141

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹2,141 each                   |
| Qty 10-24      | ₹1,927 each                   |
| Qty 25-49      | ₹1,713 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

9.00 +0.0/-0.025

|                      |                           |
|----------------------|---------------------------|
| <1                   | Centering (arcmin):       |
| 2.30 ±0.05           | Center Thickness CT (mm): |
| 1.75                 | Edge Thickness ET (mm):   |
| 8.1                  | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

|                    |                                  |
|--------------------|----------------------------------|
| Optical Properties |                                  |
| 36.00 @ 587.6nm    | Effective Focal Length EFL (mm): |
| 34.48              | Back Focal Length BFL (mm):      |
| Uncoated           | Coating:                         |
| N-BK7              | Substrate: □                     |
| 40-20              | Surface Quality:                 |
| 1.5λ               | Power (P-V) @ 632.8nm:           |
| λ/4                | Irregularity (P-V) @ 632.8nm:    |
| ±1                 | Focal Length Tolerance (%):      |
| 18.61              | Radius R <sub>1</sub> (mm):      |
| 4                  | f/#:                             |
| 0.13               | Numerical Aperture NA:           |
| 350 - 2200         | Wavelength Range (nm):           |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| Compliant                           | Reach 219:                  |
| View                                | Certificate of Conformance: |
| Japan                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Wavelength Range of 350-2200nm
- Precision Diameter and Centration Tolerances Allow for Easy OEM Integration
- Wide Variety of Diameters, Focal Lengths, and Coatings
- Anti-Reflection PCX Coating Options: [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® Uncoated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. These lenses excel in optical systems by concentrating light onto a detector or imaging plane, enhancing clarity and detail. They are also valuable for a variety of applications involving emitters, detectors, lasers, and fiber optics.

Plano-Convex lenses are ideal for a multitude of optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms. Their uncoated design ensures consistent performance across a broad wavelength range, making them versatile and reliable components for various optical setups.

TECHSPEC Uncoated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered with broadband anti-reflective (BBAR) coatings, which include [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

These coatings minimize surface reflections and maximize light transmission across different spectral ranges, ensuring optimal performance in various imaging and photonics applications. Whether for general use or specialized needs, TECHSPEC® PCX Lenses deliver precision and adaptability to enhance the effectiveness of optical systems.

Customers can utilize TECHSPEC® Uncoated Plano-Convex (PCX) Lenses in various ways:



- For emitters and detectors, these lenses are ideal for focusing and collimating light to enhance signal detection.
- In laser applications, they can be used to focus laser beams or to couple light efficiently into optical fibers, improving the performance of laser systems.
- For fiber optics, PCX lenses help couple light between fibers and other optical components, optimizing signal transmission and minimizing loss.
- In biotech instruments such as DNA sequencers and PCR testing platforms, these lenses focus light onto samples or detectors. Their ability to provide precise light collection and focusing enhances the accuracy and reliability of optical measurements, making them essential for high-resolution imaging and detection tasks.

By integrating TECHSPEC® Uncoated PCX Lenses into these systems, customers can achieve improved optical performance and enhanced functionality across various photonics and optical applications.

TECHSPEC Uncoated Plano-Convex (PCX) Lenses are available in a variety of diameters, focal lengths, and optical materials. Plano-convex lenses are manufactured from high quality materials such as UV Grade [Fused Silica](#), N-BK7 Optical Glass, and a wide variety of [Infrared \(IR\) materials](#). Different materials are useful for a variety of applications; review our [lens material selection tech note](#) for additional information.

## Technical Information



| N-BK7                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div>Uncoated N-BK7 Typical Transmission</div></div>                      | <div>Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <div><div>N-BK7 with MgF<sub>2</sub> Coating Typical Transmission</div></div> | <div>Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                              |
| <div><div>N-BK7 with VIS-EXT Coating Typical Transmission</div></div>         | <div>Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                    |
| <div><div>N-BK7 with VIS-NIR Coating Typical Transmission</div></div>         | <div>Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |

|                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                            | <a href="#">Click Here to Download Data</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <p data-bbox="596 276 974 365"><b>N-BK7 with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>       | <p data-bbox="1339 409 1843 454">Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1339 468 1850 513">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 528 1709 557"><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</p> <p data-bbox="1339 572 1839 617">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 632 1709 661"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                          |
| <p data-bbox="569 869 1037 958"><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1339 1003 1843 1047">Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p data-bbox="1339 1062 1850 1107">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 1121 1688 1151"><math>R_{abs} \leq 0.25\%</math> @ 532nm</p> <p data-bbox="1478 1151 1688 1181"><math>R_{abs} \leq 0.25\%</math> @ 1064nm</p> <p data-bbox="1478 1181 1709 1210"><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</p> <p data-bbox="1339 1225 1839 1270">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 1285 1709 1314"><a href="#">Click Here to Download Data</a></p>           |
| <p data-bbox="617 1507 1010 1596"><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>   | <p data-bbox="1339 1665 1843 1709">Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p data-bbox="1339 1724 1850 1768">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 1783 1709 1813"><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</p> <p data-bbox="1339 1828 1839 1872">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 1887 1709 1917"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                             |
| <p data-bbox="606 2145 1016 2234"><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1339 2273 1843 2318">Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p data-bbox="1339 2332 1850 2377">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 2392 1709 2421"><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm</p> <p data-bbox="1478 2421 1709 2451"><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm</p> <p data-bbox="1478 2451 1709 2481"><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</p> <p data-bbox="1339 2496 1839 2540">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1478 2555 1709 2585"><a href="#">Click Here to Download Data</a></p> |

# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---