

**TECHSPEC®**

# 920nm, 12.7mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock #26-832 **20+ In Stock**

1

MRP ₹10,594

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹10,594 each
Qty 6-25	₹9,433 each
Need More?	<a href="#">Request Quote</a>

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	<a href="#">Download All</a>

## General

**Type:** Laser Mirror

## Physical & Mechanical Properties

<b>Thickness (mm):</b>	6.35 ±0.20	<b>Diameter (mm):</b>	12.70 +0.00/-0.10
<b>Clear Aperture (%):</b>	90	<b>Back Surface:</b>	Commercial Polish
<b>Parallelism (arcmin):</b>	<3		

## Optical Properties

<b>Substrate:</b> <a href="#">Fused Silica</a> (Corning 7980)	<b>Surface Quality:</b>	10-5
<b>Angle of Incidence (°):</b>	<b>Coating:</b>	Ultrafast (870-970nm)
<b>Design Wavelength DWL (nm):</b>	<b>Wavelength Range (nm):</b>	870 - 970
<b>Surface Flatness (P-V):</b>	<b>Coating Specification:</b>	R <sub>(avg)</sub> S & P >99.90% @ 920nm @ 45° AOI R <sub>(avg)</sub> >99.7% @ 880 - 960nm @ 45° AOI
<b>Coating Type:</b> Dielectric	<b>GDD Specification:</b>	±20 fs <sup>2</sup> @ 870 - 970nm @ 45° AOI (s-pol) ±20 fs <sup>2</sup> @ 900 - 940nm @ 45° AOI (p-pol)

## Environmental & Durability Factors

**Durability:** MIL-PRF-13830B

## Regulatory Compliance

Certificate of Conformance: [View](#)

Country of Origin: United States

Imported By: Edmund Optics India Private Limited  
267, Greystone Building,  
Second Floor,  
6th Cross Rd,  
Binnamangala,  
Stage 1,  
Indiranagar,  
Bengaluru,  
Karnataka,  
India 560038  
Phone: +91-80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- GDD as Low as  $\pm 20\text{fs}^2$  at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers


TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

**Note:** Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

## Related Products




High Performance Low GDD Ultrafast Mirrors



Low GDD Dichroic Shortpass Ultrafast Filters



Ultrafast Harmonic Separators



Ultrafast Laser Mirrors

## Resources

Media Type

APPLICATION NOTE

An Introduction to Optical Coatings




TECHNICAL TOOL

Gaussian Beams Calculator

CASE STUDIES

Laser Optics for Eye Surgery

- Application Note
- Technical Tool
- Trending in Optics
- Video
- Published Article
- FAQ
- Glossary
- Scientific Paper



**APPLICATION NOTE**

### Effects of Laser Mirror Surface Flatness

**APPLICATION NOTE**

### Basics of Ultrafast Lasers

**APPLICATION NOTE**

### Highly-Dispersive Mirrors

[View More](#)