


TECHSPEC[®] 9.53 x 6.35mm 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors

Stock #39-579 CLEARANCE 10 TO 12 DAYS

− 1 +

₹7,564.65

ADD TO CART

Qty 1+

₹7,564.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
85

Back Surface:
Commercial Polish

Reflection at DWL (%) : 99.5
Coating Specification : R _{abs} >99.5% @ 266nm R _{avg} >99.5% @ 263 - 268nm
Wavelength Range (nm) : 263 - 268
Surface Flatness (P-V) : λ/10
Coating Type : Dielectric
Coating : Laser Mirror (263-268nm)
Design Wavelength DWL (nm) : 266
Dimensions (mm) : 9.53 x 6.35 +0.00/-0.10
Thickness (mm) : 3.18 ±0.20
Angle of Incidence (°) : 45
Substrate : ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference : ☐ 2.5 J/cm ² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View