

TECHSPEC® 9mm Dia. x 12mm FL, NIR I Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-125** 10 TO 12 DAYS

- 1 +

₹11,963.00

ADD TO CART

Qty 1-5
₹11,963.00
Qty 6+
₹9,570.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 -0.025

Effective Focal Length EFL (mm):
12.00 @ 587.6nm

Back Focal Length BFL (mm): 9.26
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 3 Rings
Irregularity (P-V) @ 632.8nm: 0.5 Rings
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.05
Edge Thickness ET (mm): 1.66
Radius R₁ (mm): 5.50
Clear Aperture CA (mm): 8
f/#: 1.33
Numerical Aperture NA: 0.38
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, Reference: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant