

[See all 165 Products in Family](#)

TECHSPEC<sup>®</sup> 9mm Dia. x 13.5mm FL VIS-EXT Coated, Double-Convex Lens



Stock **#89-137** **9 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹3,464

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹3,464 each                   |
| Qty 10-24      | ₹3,114 each                   |
| Qty 25-99      | ₹2,783 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

9.00 +0.000/-0.025

|                      |                                  |
|----------------------|----------------------------------|
| <1                   | Centering (arcmin):              |
| Protective as needed | Bevel:                           |
| 2.75                 | Center Thickness CT (mm):        |
| ±0.05                | Center Thickness Tolerance (mm): |
| 1.2                  | Edge Thickness ET (mm):          |
| 8.1                  | Clear Aperture CA (mm):          |

|                                      |                                             |
|--------------------------------------|---------------------------------------------|
| Optical Properties                   |                                             |
| 12.56                                | Back Focal Length BFL (mm):                 |
| 13.50                                | Effective Focal Length EFL (mm):            |
| VIS-EXT (350-700nm)                  | Coating:                                    |
| R <sub>avg</sub> <0.5% @ 350 - 700nm | Coating Specification:                      |
| N-BK7                                | Substrate: <input type="checkbox"/>         |
| 40-20                                | Surface Quality:                            |
| 1.5λ                                 | Power (P-V) @ 632.8nm:                      |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:               |
| 13.46                                | Radius R <sub>1</sub> =R <sub>2</sub> (mm): |
| 1.5                                  | f/#:                                        |
| 587.6                                | Focal Length Specification Wavelength (nm): |
| ±1                                   | Focal Length Tolerance (%):                 |
| 0.33                                 | Numerical Aperture NA:                      |
| 350 - 700                            | Wavelength Range (nm):                      |






|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 235:                  |
| Japan                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |



## Product Details

- AR Coated to Provide <0.5% Reflectance per Surface for 350 - 700nm
  - Minimize Aberrations Including Spherical and Coma
  - [UV Fused Silica DCX Lenses](#) Available
  - Other Coating Options Available: [Uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-NIR](#), and [YAG-BBAR](#)
- TECHSPEC® VIS-EXT Coated Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or cancelled due to the symmetric lens design. TECHSPEC VIS-EXT Coated Double-Convex Lenses are available in a variety of substrates and coating options for the visible and NIR spectra.

## Technical Information



|                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div data-bbox="262 68 1249 593"><h3>Uncoated N-BK7 Typical Transmission</h3></div>                        | <div data-bbox="1339 276 1843 365"><p>Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                                                                                                                                                                                                                                                              |
| <div data-bbox="262 661 1249 1151"><h3>N-BK7 with MgF<sub>2</sub> Coating Typical Transmission</h3></div> | <div data-bbox="1339 756 1843 1009"><p>Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                  |
| <div data-bbox="262 1196 1249 1774"><h3>N-BK7 with VIS-EXT Coating Typical Transmission</h3></div>       | <div data-bbox="1339 1350 1843 1602"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.5\% @ 350 - 700\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                  |
| <div data-bbox="262 1834 1249 2398"><h3>N-BK7 with VIS-NIR Coating Typical Transmission</h3></div>       | <div data-bbox="1339 1944 1843 2264"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 0.25\% @ 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |
| <div data-bbox="262 2442 1249 2884"><h3>N-BK7 with VIS 0° Coating Typical Transmission</h3></div>        | <div data-bbox="1339 2576 1843 2828"><p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                   |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>20040060080010001200</div> <div>Wavelength (nm)</div>                                                                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| <div><div>N-BK7 with YAG-BBAR Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div></div></div><div></div><div>Wavelength (nm)</div></div></div>                               | <div>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><div><math>R_{abs} \leq 0.25\%</math> @ 532nm</div><div><math>R_{abs} \leq 0.25\%</math> @ 1064nm</div><div><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>           |
| <div><div>N-BK7 with NIR I Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div></div></div><div></div><div>Wavelength (nm)</div></div></div>                                 | <div>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                              |
| <div><div>N-BK7 with NIR II Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div><div>1800</div><div>2000</div></div></div><div></div><div>Wavelength (nm)</div></div></div> | <div>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><div><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm</div><div><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm</div><div><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</div></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |

Compatible Mounts