

[See all 5 Products in Family](#)

9mm Dia. x 36mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-073 CLEARANCE 20+ In Stock

[Other Coating Options](#)

1 MRP ₹2,069

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,069 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens Type:

Physical & Mechanical Properties

9.00 +0.00/-0.10 Diameter (mm):

6.00 Centering (arcmin):

Edge Thickness ET (mm):

1.15

Clear Aperture CA (mm):

≥7.65

Optical Properties

Effective Focal Length EFL (mm):

36.00

Back Focal Length BFL (mm):

34.89

Coating:

MgF₂ (400-700nm)

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Substrate:

N-BK7

Focal Length Tolerance (%):

±1

Radius R₁ (mm):

18.61

f#:

4.00

Numerical Aperture NA:

0.13

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:



Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF₂ anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF₂ Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information



Coating Curves
