

TECHSPEC® 9mm Dia. x 36mm FL, NIR I, Inked, Double-Convex Lens



Stock #49-468-INK

17 TO 22 D=DAYS

[Other Coating Options](#)



1



₹4,394.00

ADD TO CART

Qty 1-9

₹4,394.00

Qty 10+

₹3,959.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 ±0.025

Back Focal Length BFL (mm):
35.15

Effective Focal Length EFL (mm): 36.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.55
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 36.77
Clear Aperture CA (mm): 8.1
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View