

[See all 18 Products in Family](#)

**TECHSPEC® 9mm Dia. x 36mm EFL, UV-VIS Coated, Near UV Achromatic Lens**



Stock #35-995 [CONTACT US](#)

- 1 + MRP ₹15,335

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹15,335 each
Qty 6-25	₹12,208 each
Qty 26-49	₹11,603 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Achromatic Lens **Type:**

**Physical & Mechanical Properties**

9.00 +0.0/-0.025 **Diameter (mm):**

8.1	Clear Aperture CA (mm):
<1	Centering (arcmin):
4.50 ±0.10	Center Thickness CT (mm):
3.00 ±0.05	Center Thickness CT 1 (mm):
1.50 ±0.05	Center Thickness CT 2 (mm):
3.79	Edge Thickness ET (mm):
Protective as needed	Bevel:

## Optical Properties

36.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
33.56	Back Focal Length BFL (mm):
405.00	Focal Length Specification Wavelength (nm):
19.20	Radius R <sub>1</sub> (mm):
-16.29	Radius R <sub>2</sub> (mm):
-57.12	Radius R <sub>3</sub> (mm):
<a href="#">N-FK5 / F2HT</a>	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
4	f#:
0.13	Numerical Aperture NA:
UV-VIS (345-700nm)	Coating:
R <sub>avg</sub> ≤1.5% @ 345 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
345 - 700	Wavelength Range (nm):

## Regulatory Compliance

<a href="#">Exempt</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries



- Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Excellent Transmission in 345 – 700nm Range
- Ideal for use with NUV LEDs and Mercury Lamps
- Low-Cost, Cemented Design

TECHSPEC® Near-UV (NUV) Achromatic Lenses are specifically designed to minimize the spot size for polychromatic illumination in the 345 – 700nm region. The achromatic lenses are ideal for use in fluorescence applications, as well as for simple focusing of common UV light sources, such as Mercury Arc Lamps, UV LEDs, and Tripled Nd:YAG lasers. Featuring a simple cemented design, the lenses are an excellent alternative to air-spaced doublets and triplets for the UV. TECHSPEC® Near-UV (NUV) Achromatic Lenses feature >90% transmission at 360nm and provide >50% transmission at 334nm. The lenses feature either N-FK5 or F2HT substrate and a UV-MS coating.

## Technical Information



## Compatible Mounts