

TECHSPEC<sup>®</sup> 9mm Dia. x 36mm FL UV-VIS Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#48-813** **5 In Stock**

-

1

+

₹10,743

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,743 each                  |
| Qty 6-25       | ₹8,564 each                   |
| Qty 26-49      | ₹8,096 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

9.00 +0.0/-0.025

|                      |                           |
|----------------------|---------------------------|
| <1                   | Centering (arcmin):       |
| 2.00 ±0.05           | Center Thickness CT (mm): |
| 1.38                 | Edge Thickness ET (mm):   |
| 8.1                  | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |


|                                                                              |                                                       |
|------------------------------------------------------------------------------|-------------------------------------------------------|
| Optical Properties                                                           |                                                       |
| 36.00 @ 587.6nm                                                              | Effective Focal Length EFL (mm):                      |
| 34.63                                                                        | Back Focal Length BFL (mm):                           |
| UV-VIS (250-700nm)                                                           | Coating:                                              |
| R <sub>abs</sub> ≤1.0% @ 350 - 450nm<br>R <sub>avg</sub> ≤1.5% @ 250 - 700nm | Coating Specification:                                |
| Fused Silica (Corning 7980)                                                  | Substrate: <input type="checkbox"/>                   |
| 40-20                                                                        | Surface Quality:                                      |
| 1.5λ                                                                         | Power (P-V) @ 632.8nm:                                |
| λ/4                                                                          | Irregularity (P-V) @ 632.8nm:                         |
| ±1                                                                           | Focal Length Tolerance (%):                           |
| 16.51                                                                        | Radius R <sub>1</sub> (mm):                           |
| 4                                                                            | f/#:                                                  |
| 0.13                                                                         | Numerical Aperture NA:                                |
| 250 - 700                                                                    | Wavelength Range (nm):                                |
| 3 J/cm² @ 355nm, 10ns<br>5 J/cm² @ 532nm, 10ns                               | Damage Threshold, Reference: <input type="checkbox"/> |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 235:                  |
| Japan                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |


## Product Details

- AR Coated to Provide <1.5% Reflection per Surface for 250 - 700nm
  - Precision Fused Silica Substrate
  - Various Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [UV-AR](#), [VIS-EXT](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), [NIR I](#), and [NIR II](#)
- TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses UV-VIS Coated feature precision specifications and a [variety of coating options](#) on a broadband substrate. Fused Silica is commonly used in applications from the Ultraviolet (UV) through the Near-Infrared (NIR). Its low index of refraction, low coefficient of thermal expansion, and low inclusion content make it ideal for laser applications and harsh environmental conditions. TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses UV-VIS Coated feature industry leading diameter and centration specifications, making them ideal for integration into demanding imaging and targeting applications. These lenses are UV-VIS coated to increase their coating performance in the ultraviolet and visible region.





## Technical Information






UV FS Transmission Curve



| FUSED SILICA                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| <div><h3>Uncoated Fused Silica<br/>Typical Transmission</h3><p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                                                                                                                                                                                                                                                                     |  |
| <div><h3>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</h3><p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                       |  |
| <div><h3>Fused Silica with UV-AR Coating<br/>Typical Transmission</h3><p>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 1.0\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.75\% @ 250 - 425\text{nm}</math><br/><math>R_{avg} \leq 0.5\% @ 370 - 420\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |  |

|                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>20040060080010001200</div> <div>Wavelength (nm)</div>                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <div>Fused Silica with UV-VIS Coating</div> <div>Typical Transmission</div> <div></div>    | <div>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{abs} \leq 1.0\%</math> @ 350 - 450nm</div><div><math>R_{avg} \leq 1.5\%</math> @ 250 - 700nm</div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                         |
| <div>Fused Silica with VIS-EXT Coating</div> <div>Typical Transmission</div> <div></div> | <div>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.5\%</math> @ 350 - 700nm</div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                |
| <div>Fused Silica with VIS-NIR Coating</div> <div>Typical Transmission</div> <div></div> | <div>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{abs} \leq 0.25\%</math> @ 880nm</div><div><math>R_{avg} \leq 1.25\%</math> @ 400 - 870nm</div><div><math>R_{avg} \leq 1.25\%</math> @ 890 - 1000nm</div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |
| <div>Fused Silica with VIS 0° Coating</div> <div>Typical Transmission</div> <div></div>  | <div>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.4\%</math> @ 425 - 675nm</div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                 |

|                                                                                                                                                                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div><div><div>Fused Silica with YAG-BBAR Coating</div><div>Typical Transmission</div><div></div></div></div> | <div><p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><div><div><math>R_{abs} \leq 0.25\%</math> @ 532nm</div><div><math>R_{abs} \leq 0.25\%</math> @ 1064nm</div><div><math>R_{avg} \leq 1.0\%</math> @ 500 - 1100nm</div></div><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>           |
| <div><div><div>Fused Silica with NIR I Coating</div><div>Typical Transmission</div><div></div></div></div>   | <div><p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><div><div><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</div></div><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                   |
| <div><div><div>Fused Silica with NIR II Coating</div><div>Typical Transmission</div><div></div></div></div> | <div><p>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><div><div><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm</div><div><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm</div><div><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</div></div><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts