

TECHSPEC® 9mm Dia. x 40mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-317** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹6,612.00**

ADD TO CART

Qty 1-5
₹6,612.00
Qty 6+
₹5,285.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
40.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 37.54
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 8.1
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.06 ±0.10
Center Thickness CT 1 (mm) : 3.73 ±0.05
Center Thickness CT 2 (mm) : 1.33 ±0.05
Radius R₁ (mm) : 24.77
Radius R₂ (mm) : -18.01
Radius R₃ (mm) : -51.17
Edge Thickness ET (mm) : 4.45
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 4.44
Numerical Aperture NA : 0.11
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

Reach 181 : Compliant
RoHS 2015 : Compliant
Certificate of Conformance : View