

TECHSPEC® 9mm Dia. x 36mm FL, VIS-NIR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#63-826** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹11,528.00

ADD TO CART

Qty 1-5

₹11,528.00

Qty 6+

₹9,222.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Back Focal Length BFL (mm):

35.31
Effective Focal Length EFL (mm): 36.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00 ±0.05
Edge Thickness ET (mm): 1.38
Radius R₁=R₂ (mm): 32.69
Clear Aperture CA (mm): 8.1
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, Reference:  5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant