

TECHSPEC® 9mm Dia. x 75mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-820** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹5,829.00

ADD TO CART

Qty 1-5

₹5,829.00

Qty 6+

₹4,655.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):

75.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 72.35
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 8.1
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.60 ±0.10
Center Thickness CT 1 (mm) : 3.00 ±0.05
Center Thickness CT 2 (mm) : 1.60 ±0.05
Radius R₁ (mm) : 46.44
Radius R₂ (mm) : -33.77
Radius R₃ (mm) : -95.94
Edge Thickness ET (mm) : 4.28
Substrate: N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 8.33
Numerical Aperture NA : 0.06
Coating : MgF ₂ (400-700nm)
Coating Specification : R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View