


[See all 6 Products in Family](#)

ESD 1.2mm Tip Width, Non-Marring Tweezers



Resin 1.2mm Tip Width, Non-Marring Tweezers, #36-449



Stock **#36-447** **5 In Stock**

1 MRP ₹4,912

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹4,912 each
Qty 10+	₹4,381 each
Need More?	Request Quote

Product Downloads

General

ESD Tweezer **Type:**

Physical & Mechanical Properties

125.00 **Length (mm):**

20	Weight (g):
1.2	Tip Width (mm):
10	Tip to Tip Distance, Open (mm):
150	Holding Strength (g):

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- ESD Design Features Stainless Steel Body and Ceramic Tips
- Resin-Tip Design Features Aluminum Body and Plastic Tips
- Ceramic Design Features Polyacetal Body and Ceramic Tips

These high quality tweezers are ideal for handling small optics or electronics since the tips reduce slipping and eliminate damage to delicate surfaces. We highly recommend the ESD model or the Resin-Tip model with the interchangeable replacement ESD tips for optics. Tips are interchangeable for all ESD and Resin-Tip models. Ceramic tips offer excellent wear resistance. All tips are non-magnetic.

ESD: Tips are fine ceramic (containing carbon), body is stainless steel. Tips have max operating temperature of 160°C and are conductive with a surface resistance of $10^8 - 10^{11}\Omega$. Tips are black. Two choices for tip size.

Resin-Tip: Tips are PBT plastic (containing glass), body is aluminum. Lightweight body provides comfort for extended use. Tips have max operating temperature of 190°C. Tips are white and are non-conductive.

Ceramic: Tips are fine ceramic, body is polyacetal (with glass fiber reinforcement). Tips are non-magnetic, non-conductive, and heat/chemical resistant.