

## Acrylic Filter 915nm 3mm thick, M30.5



Stock #72-110 **2 In Stock**

MRP ₹8,929

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹8,929 each                   |
| Qty 10+        | ₹8,475 each                   |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

25.50 **Clear Aperture CA (mm):**

32.50 **Outer Diameter (mm):**

**Construction:**

Mounted in Black Anodized Ring

**Substrate Thickness (mm):**

1.00 & 3.00

## Optical Properties

**Minimum Transmission (%):**

≥90

**Coating:**

OLEO AR Coated Coating applied to both surfaces

**Transmission Wavelength (nm):**

960-1650, 1750-1890, 1925-2090

## Threading & Mounting

**Filter Thread:**

M30.5 x 0.50

**Mount Thickness (mm):**

5.2

**Mount Thickness Including Threads (mm):**

7.0

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 242:**

[Compliant](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- High Efficiency, Oleophobic Anti-Reflection Coating
- M22.5 through M105 Threaded Mount Options Available
- For Imaging Applications in the UV, VIS, and NIR Ranges

Acrylic Protective Longpass Filters cover the UV, VIS, and NIR spectral ranges and are designed with high-efficiency, anti-reflection oleophobic coatings that resist smudging, minimize light loss, and enhance performance. These filters offer a cost-effective way to protect expensive lenses and lighting from dirt, dust, liquids, impacts, and harsh conditions while maintaining image quality. Mounted in threaded mounts ranging from M22.5 to M105, these filters can be easily integrated into a variety of imaging applications. Acrylic Protective Longpass Filters achieve high transmission rates, typically exceeding 90% within their designed wavelength range. These filters are ideal for a diverse range of imaging applications such as industrial camera housings, dashboard cameras, LCD screen protection, and thermal uses as well as FDA and EFSA applications where the use of glass is not permitted and thickness is a concern.