

[See all 138 Products in Family](#)

# Allied Vision Alvium 1800 U-1240m, 1/1.7" 12.22MP S-Mount, USB 3.0 Monochrome Camera

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock **#23-182** **1 In Stock**

[Similar Cameras](#)

1 MRP ₹46,728

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹46,728 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

**Spectrum:**  
Monochrome

## General

**Type:**  
Monochrome Camera

**Model Number:**  
1800 U-1240m

Allied Vision	<b>Manufacturer:</b>
Alvium	<b>Camera Series:</b>

## Physical & Mechanical Properties

33 x 29 x 29 (includes connectors and lens mount)	<b>Dimensions (mm):</b>
65	<b>Weight (g):</b>

Full	<b>Housing:</b>
------	-----------------

## Sensor

256KB	<b>Image Buffer:</b>
1/1.7"	<b>Sensor Format:</b>

12.22	<b>Resolution (Megapixels):</b>
29.00	<b>Frame Rate (fps):</b>

4,024 x 3,036	<b>Pixels (H x V):</b>
1.85 x 1.85	<b>Pixel Size, H x V (µm):</b>

7.4 × 5.6	<b>Sensing Area, H x V (mm):</b>
Sony IMX226	<b>Imaging Sensor:</b>

Progressive Scan CMOS	<b>Type of Sensor:</b>
RS, Global reset shutter (GRS)	<b>Shutter Type:</b>

8/10 bit	<b>Pixel Depth:</b>
13µs - 10s	<b>Exposure Time:</b>

65	<b>Dynamic Range (dB):</b>
USB3 Vision v1.0, GenICam	<b>Machine Vision Standard:</b>

## Electrical

3.10	<b>Power Consumption (W):</b>
------	-------------------------------

## Hardware & Interface Connectivity

USB 3.0 Gen 1	<b>Interface:</b>
USB 3.0 Gen 1, Micro-B	<b>Connector:</b>

Power over USB or via GPIO	<b>Power Supply:</b>
4 Programmable TTL GPIOs	<b>GPIOs:</b>

Hardware Trigger (GPIO) or Software Trigger	<b>Synchronization:</b>
Back Panel	<b>Interface Port Orientation:</b>

7-pin JST	<b>GPIO Connector Type:</b>
-----------	-----------------------------

## Threading & Mounting

S-Mount (M12 x 0.5)	<b>Mount:</b>
1/4-20 and M6 with Tripod Mount Adapter <a href="#">#14-156</a>	<b>Mounting Threads:</b>

## Environmental & Durability Factors

-20 to +65 (housing temperature)	<b>Operating Temperature (°C):</b>
-20 to +85	<b>Storage Temperature (°C):</b>

## Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Compliant

Reach 240:

Germany

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Alvium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Alvium USB 3.0 Cameras feature a lightweight compact form factor with ALVUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.

;