

[See all 138 Products in Family](#)

Allied Vision Alvium 1800 U-291c, 2/3" 2.9MP, USB 3.0 Color Camera (Board Level)

See More by [Allied Vision](#)



Allied Vision Alvium USB 3.1 Cameras



Stock #23-171 [CONTACT US](#)

[Similar Cameras](#)

1 MRP ₹78,588

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹78,588 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

1800 U-291c **Model Number:**

Allied Vision **Manufacturer:**
Alvium **Camera Series:**

Physical & Mechanical Properties

Dimensions (mm):
38 x 29 x 29 (includes connectors and lens mount)
Weight (g):
50

Housing:
Board Level

Sensor

Image Buffer:
256KB
Sensor Format:
2/3"

Resolution (Megapixels):
2.91
Frame Rate (fps):
144.00

Pixels (H x V):
1,944 x 1,472
Pixel Size, H x V (µm):
4.5 x 4.5

Sensing Area, H x V (mm):
8.8 x 6.6

Imaging Sensor:
Sony IMX421

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
8/10/12 Bit

Exposure Time:
16µs - 10s

Machine Vision Standard:
USB3 Vision v1.0, GenICam

Electrical

Power Consumption (W):
4.00

Hardware & Interface Connectivity

Interface:
USB 3.0 Gen 1

Connector:
USB 3.0 Gen 1, Micro-B

Power Supply:
Power over USB or via GPIO

GPIOs:
4 Programmable TTL GPIOs

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:
Back Panel

GPIO Connector Type:
7-pin JST

Threading & Mounting

Mount:
No Lens Mount

Mounting Threads:
1/4-20 and M6 with Tripod Mount Adapter [#14-156](#)

Environmental & Durability Factors

Operating Temperature (°C):
-20 to +85 (mainboard temperature)

Storage Temperature (°C):
-20 to +85

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Germany

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Alvium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Alvium USB 3.0 Cameras feature a lightweight compact form factor with ALVUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.