

[See all 138 Products in Family](#)

Allied Vision Alvium 1800 U-508c, 2/3" 5.07MP C-Mount, USB 3.0 Color Camera

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Full Housing (Front)



Stock **#17-088** **3 In Stock**

[Similar Cameras](#)

1 MRP ₹1,27,440

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,27,440 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

1800 U-508c **Model Number:**

Allied Vision
Alvium

Manufacturer:
Camera Series:

Physical & Mechanical Properties

38 x 29 x 29 (includes connectors and lens mount)

60

Dimensions (mm):
Weight (g):

Full

Housing:

Sensor

256KB

2/3"

5.07

85.00

2,464 x 2,056

3.45 x 3.45

8.5 x 7.1

Sony IMX250

Progressive Scan CMOS

Global

8/10/12 Bit

177µs - 10s

72

USB3 Vision v1.0, GenICam

Image Buffer:
Sensor Format:
Resolution (Megapixels):
Frame Rate (fps):
Pixels (H x V):
Pixel Size, H x V (µm):
Sensing Area, H x V (mm):
Imaging Sensor:
Type of Sensor:
Shutter Type:
Pixel Depth:
Exposure Time:
Dynamic Range (dB):
Machine Vision Standard:

Electrical

2.9

Power Consumption (W):

Hardware & Interface Connectivity

USB 3.0 Gen 1

USB 3.0 Gen 1, Micro-B

Power over USB or via GPIO

4 Programmable TTL GPIOs

Hardware Trigger (GPIO) or Software Trigger

Back Panel

7-pin JST

Interface:
Connector:
Power Supply:
GPIOs:
Synchronization:
Interface Port Orientation:
GPIO Connector Type:

Threading & Mounting

C-Mount

1/4-20 and M6 with Tripod Mount Adapter [#14-156](#)

Mount:
Mounting Threads:

Environmental & Durability Factors

-20 to +65 (housing temperature)

-20 to +85

Operating Temperature (°C):
Storage Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Germany

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Alvium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Alvium USB 3.0 Cameras feature a lightweight compact form factor with ALVUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.