

[See all 127 Products in Family](#)

# Allied Vision Alvium 1800 U-511c, 1/1.8" 5.1MP S-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)

See More by [Allied Vision](#)



Stock #19-582 **1 In Stock**

[Similar Cameras](#)

- 1 + MRP ₹72,216

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹72,216 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads

Color

Spectrum:

**General**

Color Camera	<b>Type:</b>
1800 U-511c	<b>Model Number:</b>
Allied Vision	<b>Manufacturer:</b>
Alvium Right Angle	<b>Camera Series:</b>

## Physical & Mechanical Properties

25 x 32 x 29 (includes connectors and lens mount)	<b>Dimensions (mm):</b>
50	<b>Weight (g):</b>
Partial	<b>Housing:</b>

## Sensor

256KB	<b>Image Buffer:</b>
1/1.8"	<b>Sensor Format:</b>
5.10	<b>Resolution (Megapixels):</b>
66.00	<b>Frame Rate (fps):</b>
2,464 x 2,064	<b>Pixels (H x V):</b>
2.74 x 2.74	<b>Pixel Size, H x V (µm):</b>
6.8 x 5.7	<b>Sensing Area, H x V (mm):</b>
Sony IMX547	<b>Imaging Sensor:</b>
Progressive Scan CMOS	<b>Type of Sensor:</b>
Global	<b>Shutter Type:</b>
8/10/12 Bit	<b>Pixel Depth:</b>
164µs - 10s @ 450 MBps 163µs - 10s @ 200 MBps	<b>Exposure Time:</b>
Not Specified	<b>Dynamic Range (dB):</b>
USB3 Vision v1.0, GenICam	<b>Machine Vision Standard:</b>

## Electrical

3.2	<b>Power Consumption (W):</b>
-----	-------------------------------

## Hardware & Interface Connectivity

USB 3.1 Gen 1	<b>Interface:</b>
USB 3.1 Gen 1, Micro-B	<b>Connector:</b>
Power over USB or via GPIO	<b>Power Supply:</b>
4 Programmable TTL GPIOs	<b>GPIOs:</b>
Hardware Trigger (GPIO) or Software Trigger	<b>Synchronization:</b>
Back Panel (Right Angle)	<b>Interface Port Orientation:</b>
7-pin JST	<b>GPIO Connector Type:</b>

## Threading & Mounting

S-Mount (M12 x 0.5)	<b>Mount:</b>
¼-20 and M6 with Tripod Mount Adapter <a href="#">#14-156</a>	<b>Mounting Threads:</b>

## Environmental & Durability Factors

+5 to +65 **Operating Temperature (°C):**

-10 to +70 **Storage Temperature (°C):**

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Compliant](#)

**Country of Origin:**  
Germany

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Right Angle USB Port Orientation
- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- [Allied Vision Alvium USB 3.1 Cameras](#) Also Available

Allied Vision Alvium Right Angle USB 3.1 Cameras feature ALVUM® System on Chip (SoC) technology and a right-angle USB port in a lightweight compact form factor, offering a comprehensive image processing library for advanced onboard image correction, preprocessing functions to relieve host computer and processor workload, and allow for easy system integration. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium Right Angle USB 3.1 Cameras feature a 90° right angle USB port and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

**Note:** Board level versions do not have a lens mount.