

[See all 61 Products in Family](#)

Allied Vision Alvium G1-319m, 1/1.8" 3.2MP C-Mount, GigE PoE Monochrome Camera

See More by [Allied Vision](#)



Stock #23-547 [CONTACT US](#)

[Similar Cameras](#)

1 MRP ₹61,596

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹61,596 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

Avium G1-319m	Model Number:
Allied Vision	Manufacturer:
Avium G1	Camera Series:

Physical & Mechanical Properties

41 x 29 x 29	Dimensions (mm):
65	Weight (g):
Full	Housing:

Sensor

32MB	Image Buffer:
1/1.8"	Sensor Format:
3.20	Resolution (Megapixels):
36.00	Frame Rate (fps):
2,064 x 1,544	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
7.1 x 5.3	Sensing Area, H x V (mm):
Sony IMX265	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
49µs - 10s	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision V2.2, GenICam V2.0	Machine Vision Standard:

Electrical

External power: 3.0 W at 12 VDC Power over Ethernet: 3.3 W	Power Consumption (W):
--	-------------------------------

Hardware & Interface Connectivity

GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
10-pin TFM	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
¼"-20 and M6 with Tripod Mount Adapter #14-156	Mounting Threads:

Environmental & Durability Factors

	Operating Temperature (°C):
--	------------------------------------

-20 to +50

Storage Temperature (°C):

-20 to +85

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Germany

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 24.6MP Resolution with Framrates up to 276FPS
- Robust Industrial GigE Vision Interface with PoE
- Onboard Image Processing and Expansive Feature Sets
- Alvim G5 and [Allied Vision Alvim USB 3.1 Cameras](#) Also Available

Allied Vision Alvim G1 GigE PoE Cameras feature a lightweight, compact form factor and combines the advantages of the established GigE Vision standard with the flexibility of the Alvim platform. The ALVUM® System on Chip (SoC) technology offers a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. These cameras feature the latest industrial standard hardware and can easily be integrated into any vision system while ensuring long-term availability and reliability. With precision sensor alignment, enhanced cleanliness, fixed pattern noise correction, and defect pixel correction, resolutions up to 24.6MP and framerates up to 276 FPS are available. Allied Vision Alvim G1 GigE PoE Cameras feature a gigabit ethernet port on the back panel and are available in a variety of monochrome and color options with either C-Mount or S-Mount lens interfaces.