

[See all 45 Products in Family](#)

Allied Vision Alvium G5-2040m, 1.1" 20.4MP CS-Mount, 5GigE PoE Monochrome Camera

See More by [Allied Vision](#)



Stock **#26-347** **1 In Stock**

-

1

+

₹2,40,000

ADD TO CART

Volume Pricing	
Qty 1+	₹2,40,000 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
Alvium G5-2040m	Model Number:
Allied Vision	Manufacturer:

Alvium G5	Camera Series:
Physical & Mechanical Properties	
55 × 29 × 29	Dimensions (mm):
95	Weight (g):
Full	Housing:
Sensor	
512KB	Image Buffer:
1.1"	Sensor Format:
20.40	Resolution (Megapixels):
24.00	Frame Rate (fps):
4,512 x 4,512	Pixels (H x V):
2.74 x 2.74	Pixel Size, H x V (µm):
12.36 x 12.36	Sensing Area, H x V (mm):
Sony IMX541	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
20 µs to 10 s	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision V2.2, GenICam V2.0	Machine Vision Standard:
Electrical	
External power: 6.9 W at 12 VDC Power over Ethernet: 7.6 W	Power Consumption (W):
Hardware & Interface Connectivity	
5GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
10-pin TFM	GPIO Connector Type:
Threading & Mounting	
CS-Mount	Mount:
¼"-20 and M6 with Tripod Mount Adapter #14-156	Mounting Threads:
Environmental & Durability Factors	
+5 to +60	Operating Temperature (°C):
-20 to +85	Storage Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Germany	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- 4.2 Times More Bandwidth than GigE
- Up to 24.6MP Resolution with Framerrates up to 691 FPS
- Onboard Image Processing and Expansive Feature Sets

Allied Vision Alvium G5 5GigE PoE Cameras feature a lightweight, compact form factor and combines the advantages of the established 5GigE VSION standard with the flexibility of the Alvium platform. Powered by ALVUM® Technology, the sugar cube style camera delivers high image quality at a low power consumption. These cameras feature the latest industrial standard hardware and can easily be integrated into any USB3 VSION or GigE VSION system while ensuring long-term availability and reliability. With precision sensor alignment, enhanced cleanliness, fixed pattern noise correction, and defect pixel correction, resolutions up to 24.6MP and framerates up to 691 FPS are available. Allied Vision Alvium G5 5GigE PoE Cameras feature a gigabit ethernet port on the back panel and are available in a variety of monochrome and color options with either C-Mount or S-Mount lens interfaces all in the compact sugar cube format.