


[See all 69 Products in Family](#)

Basler ace acA4112-8gm Monochrome GigE Camera

See More by [Basler](#)



Basler ace GigE Cameras



Stock #37-211 [CONTACT US](#)

[Similar Cameras](#)

1 MRP ₹2,18,772

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,18,772 each
Need More?	Request Quote

Product Downloads

Spectrum:
Monochrome

General

Type:
Monochrome Camera

Model Number:
acA4112-8gm

Basler
ace

Manufacturer:
Camera Series:

Physical & Mechanical Properties

50 x 40 x 30 (excludes connectors and lens mount)

Dimensions (mm):
Weight (g):

90

Full

Housing:

Sensor

1.1"

Sensor Format:
Resolution (Megapixels):

12.00

8.00

Frame Rate (fps):
Pixels (H x V):

4,096 x 3,000

3.45 x 3.45

Pixel Size, H x V (µm):
Sensing Area, H x V (mm):

14.13 x 10.35

Sony IMX304

Imaging Sensor:
Type of Sensor:

Progressive Scan CMOS

Global

Shutter Type:
Pixel Depth:

8/12 bit

Programmable via camera API, hardware trigger

Exposure Time:
Dynamic Range (dB):

72.8

GigE Vision, GenICam

Machine Vision Standard:

Electrical

2.7 (12VDC External Power Supply)
3.2 (PoE)

Power Consumption (W):

Hardware & Interface Connectivity

GigE (PoE)

Interface:
Connector:

GigE, RJ45 with Screw Locks

Power Supply Required and Sold Separately.
USA: [#68-466](#)
Europe: [#68-466](#)
Japan: [#68-466](#)
Korea: [#68-466](#)
China: [#68-466](#)

Power Supply:

1 opto-coupled input line, 1 opto-coupled output line, 1 general purpose I/O (GPIO) line

GPIOs:

Hardware Trigger (GPIO), Software Trigger, or Free-Run

Synchronization:

Back Panel

Interface Port Orientation:

6-pin Hirose (HR10)

GPIO Connector Type:

Threading & Mounting

C-Mount

Mount:
Mounting Threads:

1/4-20 with Tripod Mount Adapter [#17-711](#)

Environmental & Durability Factors

Operating Temperature (°C):

0 to +50

Storage Temperature (°C):

-20 to +80

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 253:

[Contains SVHC\(s\)](#)

Country of Origin:

Germany

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Perfect Analog Replacement
- Ultra-Small Form Factor
- Power Over Ethernet (PoE)
- Includes Basler Pylon Driver

Basler ace GigE Cameras are economical Gigabit Ethernet cameras that provide an ideal upgrade opportunity for analog camera users. With a small form factor matching that of many analog cameras (29 x 29mm), the ace can be a drop-in replacement to an existing analog system or a great choice to start a new project. Basler ace GigE Cameras can use Power Over Ethernet (PoE) (2 GigE cables required). The cameras can have long cable lengths and are the optimal choice for use on a factory floor. All cameras include the industry-proven Basler Pylon SDK Software and Driver.

Technical Information



MT9P031 Sensor QE Curve