

[See all 93 Products in Family](#)

Basler ace2 a2A2048-37gcPRO Color GigE Pro Camera

See More by [Basler](#)



Basler ace2 GigE Cameras (Front)



Stock **#74-926** NEW [CONTACT US](#)

-

1

+

MRP ₹55,950

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹55,950 each
Need More?	Request Quote

Product Downloads

Color		Spectrum:
Color Camera		Type:
a2A2048-38gcPRO		Model Number:

Basler	Manufacturer:
Ace2	Camera Series:

Physical & Mechanical Properties

48.9 x 29 x 29 mm	Dimensions (mm):
<100	Weight (g):
Full	Housing:

Sensor

1/3.1"	Sensor Format:
3.20	Resolution (Megapixels):
37.00	Frame Rate (fps):
2,064 x 1,552	Pixels (H x V):
2.25 x 2.25	Pixel Size, H x V (µm):
4.6 x 3.5	Sensing Area, H x V (mm):
Sony IMX900	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
hardware trigger & freely programmable	Exposure Time:
GigE Vision 2.0, GenICam	Machine Vision Standard:

Hardware & Interface Connectivity

GigE	Interface:
USB, RJ45 with Screw Locks	Connector:
PoE or 12-24 VDC	Power Supply:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Ethernet connection, or Free Run	Synchronization:
Back Panel	Interface Port Orientation:
M8 6-pin	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #16-641	Mounting Threads:

Environmental & Durability Factors

-10 °C - 60 °C	Operating Temperature (°C):
----------------	-----------------------------

Regulatory Compliance


View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala,	Imported By:

Product Details


- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace GigE Cameras](#) Also Available

Basler ace2 GigE/5GigE Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust M8 connector. The Basler ace2 GigE/5GigE Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (GigE Vision 2.0) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both GigE, 5GigE and USB3.0 interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.


Technical Information




IMX676 Sensor QE Curve



IMX900 Sensor QE Curve



GMAX2505 Sensor QE Curve



IMX546 Sensor QE Curve



IMX545 Sensor QE Curve



GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve