

[See all 93 Products in Family](#)

Basler ace2 a2A3840-13gmBAS Monochrome GigE Basic Camera

See More by [Basler](#)



Basler ace2 GigE Cameras (Front)



Stock **#16-597** [CONTACT US](#)

[Similar Cameras](#)

-

1

+

₹35,000

ADD TO CART

Volume Pricing	
Qty 1+	₹35,000 each
Need More?	Request Quote

Product Downloads

Monochrome		Spectrum:
Monochrome Camera		Type:
a2A3840-13gmBAS		Model Number:

Basler	Manufacturer:
ace2	Camera Series:
Physical & Mechanical Properties	
55.5 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
<100	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
1/1.8"	Sensor Format:
8.30	Resolution (Megapixels):
13.00	Frame Rate (fps):
3,840 x 2,160	Pixels (H x V):
2.00 x 2.00	Pixel Size, H x V (µm):
7.7 x 4.3	Sensing Area, H x V (mm):
Sony IMX334	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling	Shutter Type:
8/10/12 Bit	Pixel Depth:
Freely Programmable	Exposure Time:
69.2	Dynamic Range (dB):
GigE Vision 2.0, GenICam	Machine Vision Standard:
Electrical	
2.9	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power over Ethernet (PoE) or via GPIO with #16-644	Power Supply:
1 opto-coupled input line, 2 general purpose I/O (GPIO) lines	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin M8	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #16-641	Mounting Threads:
Environmental & Durability Factors	
-10 to +60	Operating Temperature (°C):
-20 to +80	Storage Temperature (°C):

Regulatory Compliance

Compliant

View

Compliant

Germany


Edmund Optics India Private Limited

Product Details


- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- **Basler ace GigE Cameras** Also Available

Basler ace2 GigE/5GigE Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust M8 connector. The Basler ace2 GigE/5GigE Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (GigE Vision 2.0) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both GigE, 5GigE and USB3.0 interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.


Technical Information



IMX676 Sensor QE Curve



IMX900 Sensor QE Curve



GMAX2505 Sensor QE Curve



IMX546 Sensor QE Curve



IMX545 Sensor QE Curve



GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve