

[See all 14 Products in Family](#)

## Broadband NIR Polarizing Film 76mm Sq



Stock #71-128 **15 In Stock**

- 1 + MRP ₹73,146

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹73,146 each                  |
| Qty 10-25      | ₹65,831 each                  |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Linear Polarizer **Type:**

**Note:**  
Protective film both sides, polarization axis indicated but cutout on polarizer edge

### Physical & Mechanical Properties

76.00 **Length (mm):**

|                 |                                    |
|-----------------|------------------------------------|
| 76 x 76         | <b>Dimensions (mm):</b>            |
| 0.58 ±0.1       | <b>Thickness (mm):</b>             |
| +/- 0.25        | <b>Dimensional Tolerance (mm):</b> |
| Polarizing Film | <b>Construction:</b>               |
| 76.00           | <b>Width (mm):</b>                 |

## Optical Properties

|  |                                   |
|--|-----------------------------------|
| Uncoated   | <b>Coating:</b>                   |
| 5,000:1 (400-760nm), 1350:1 (760-2200nm)<br>Average, typical                           | <b>Extinction Ratio:</b>          |
| Polymer Film on TAC  | <b>Substrate:</b> □               |
| Single: 26(400-760nm) 40(760-2200nm) Crossed:<br>0.0005 (400-760nm) 0.029 (760-2200nm) | <b>Transmission (%):</b>          |
| 400 - 2200   | <b>Wavelength Range (nm):</b>     |
| 26(400-760nm) 40(760-2200nm)   | <b>Transmission, Single (%):</b>  |
| 0.0005 (400-760nm) 0.029 (760-2200nm)  | <b>Transmission, Crossed (%):</b> |

## Environmental & Durability Factors

|  |                                    |
|--|------------------------------------|
| Heat Resistance 70°C Dry Cold Resistance -51°C | <b>Operating Temperature (°C):</b> |
|--|------------------------------------|

## Regulatory Compliance

|   |                                    |
|---|------------------------------------|
| <a href="#">Compliant</a>   | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>  | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a>   | <b>Reach 240:</b>                  |
| United States   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |


## Product Details

- Ideal for NIR Polarization Applications
- >400:1 Extinction Ratio from 800 - 2200nm
- High Efficiency Across Wavelength Range
- Durable Polymer Substrate

Near-Infrared (NIR) Linear Polarizing Film consists of a durable polymer substrate and is ideal for imaging applications that range from the visible to NIR (400 - 2200nm). This polarizing polymer film features an excellent average transmission of 39% with greater than 99.6% polarization efficiency for incident randomly polarized light between 760 and 2200nm. Multiple rectangular sizes are available to accommodate light sources that range from low power NIR lasers with small beam diameters, to larger LED light beams. Near-Infrared (NIR) Linear Polarizing Film is used in industrial imaging and laboratory applications, i.e. to attenuate the intensity of low output NIR lasers and LEDs or to reduce glare in images recorded using NIR photodetectors. The polarization axis is labelled on the protective masking of the polarizing polymer film for rectangular parts and as a notch cutout on the polarizing polymer film for circular parts.

**Note:** Remove protective masking before first use.

## Technical Information



NIR Linear Polarizing Film



;