


Broadband NIR Polarizing Film 75mm Dia



Stock **#71-127** 20+ In Stock

-

1

+

₹50,603

ADD TO CART

Volume Pricing	
Qty 1-9	₹50,603 each
Qty 10+	₹45,542 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Linear Polarizer

Type:

Protective film both sides, polarization axis indicated but cutout on polarizer edge

Note:

Physical & Mechanical Properties	
75.00 +/- 0.25	Diameter (mm):
0.58 ±0.1	Thickness (mm):
+/- 0.25	Dimensional Tolerance (mm):
Polarizing Film	Construction:
Optical Properties	
Uncoated	Coating:
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	Extinction Ratio:
Polymer Film on TAC	Substrate: □
Single: 26(400-760nm) 40(760-2200nm) Crossed: 0.0005 (400-760nm) 0.029 (760-2200nm)	Transmission (%):
400 - 2200	Wavelength Range (nm):
26(400-760nm) 40(760-2200nm)	Transmission, Single (%):
0.0005 (400-760nm) 0.029 (760-2200nm)	Transmission, Crossed (%):
Environmental & Durability Factors	
Heat Resistance 70°C Dry Cold Resistance -51°C	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Ideal for NIR Polarization Applications
- >400:1 Extinction Ratio from 800 - 2200nm
- High Efficiency Across Wavelength Range
- Durable Polymer Substrate

Near-Infrared (NIR) Linear Polarizing Film consists of a durable polymer substrate and is ideal for imaging applications that range from the visible to NIR (400 - 2200nm). This polarizing polymer film features an excellent average transmission of 39% with greater than 99.6% polarization efficiency for incident randomly polarized light between 760 and 2200nm. Multiple rectangular sizes are available to accommodate light sources that range from low power NIR lasers with small beam diameters, to larger LED light beams. Near-Infrared (NIR) Linear Polarizing Film is used in industrial imaging and laboratory applications, i.e. to attenuate the intensity of low output NIR lasers and LEDs or to reduce glare in images recorded using NIR photodetectors. The polarization axis is labelled on the protective masking of the polarizing polymer film for rectangular parts and as a notch cutout on the polarizing polymer film for circular parts.

Note: Remove protective masking before first use.

TECHNICAL INFORMATION

