

TECHSPEC[®] C-Mount Achromat Pair 1:1 with 30 and 30mm Focal Lengths



Stock #87-185 2 In Stock

-

1

+

₹29,972

ADD TO CART

Volume Pricing	
Qty 1-5	₹29,972 each
Qty 6-25	₹23,978 each
Qty 26-49	₹23,199 each
Need More?	Request Quote

Product Downloads

General	
Relay Lens	Type:
Physical & Mechanical Properties	
0.8 - 20	Aperture (mm):
38.00	Housing Diameter (mm):


45.9	Housing Length (mm):
13.00	Image Distance (mm):
Optical Properties	
40-20	Surface Quality:
f/1.4 - f/37	Working f#:
VS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @ 425 - 675nm	Coating Specification:
30.0	Effective Focal Length EFL A (mm):
30.0	Effective Focal Length EFL B (mm):
1:1	Magnification:
15.00	Object Distance (mm):
425 - 675	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- C-Mount Designs for Easy Integration into Imaging Applications
- Feature Integrated Iris for Increased Control of Light Throughput
- Ideal for Relay or Projection Applications

TECHSPEC® C-Mount Achromatic Pairs are designed to be easily integrated into a variety of OEM applications. TECHSPEC C-Mount Achromatic Pairs utilize an integrated iris to allow for user adjustment of numerical aperture and depth of focus. Each lens has been oriented for maximum system performance. The aluminum housing removes the risks associated with handling loose optics. Broadband visible coated lenses provide high transmission and low reflection loss over wide spectral regions.

Technical Information



Coating Curves