

[See all 13 Products in Family](#)

C6205, 1.4" Color, Teledyne DALSA Genie Nano 10GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano 10GigE Cameras - Front



Stock **#28-677** **1 In Stock**

- 1 +

MRP ₹6,03,641

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹6,03,641 each
Need More?	Request Quote

Product Downloads

Color		Spectrum:
Color Camera		Type:
G6-GC31-C6205		Model Number:

Teledyne DALSA	Manufacturer:
Genie Nano-10GigE	Camera Series:
Physical & Mechanical Properties	
59 x 59 x 41 (excludes connectors and lens mount)	Dimensions (mm):
183	Weight (g):
Full	Housing:
Sensor	
1.4"	Sensor Format:
37.70	Resolution (Megapixels):
18.50	Frame Rate (fps):
6,144 x 6,144	Pixels (H x V):
2.50 x 2.50	Pixel Size, H x V (µm):
15.35 x 15.36	Sensing Area, H x V (mm):
Teledyne e2v Emerald 36M	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10 bit	Pixel Depth:
Automatic, Programmable, or via External Trigger	Exposure Time:
62.00	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:
Electrical	
12.5	Power Consumption (W):
Hardware & Interface Connectivity	
10GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #88-063 Europe: #88-063 Japan: #88-063 Korea: Not Available China: #88-063	Power Supply:
2 opto-isolated input, 3 opto-isolated output	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Threading & Mounting	
M42-Mount	Mount:
1/4-20 with Tripod Mount Adapter #34-966	Mounting Threads:
Environmental & Durability Factors	
-20 to +60	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):

Regulatory Compliance	
-----------------------	--

Exempt

RoHS 2015:

View

Certificate of Conformance:

Contains SVHC(s)

Reach 235:

Canada

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 67.10 MP Resolution with Framerates up to 18.50FPS
- Supports Trigger-to-Image Reliability (T2IR) Framework
- Compact (44 x 59 x 59mm), M42-Mount, Lightweight, and Robust All Metal Design



Teledyne
Authorized
Distributor

Teledyne DALSA Genie™ Nano 10GigE Cameras are designed with the 10GBASE-T (10GigE) Ethernet Interface and can also run at ethernet link speeds of 1, 2.5, or 5GigE. These M42-mount cameras are available with either the Teledyne e2v Emerald 36M sensor featuring a 1.4" format or the Teledyne e2v Emerald 67M sensor which features an APS-C format. Genie™ Nano cameras support Sapera LT SDKs and 3rd Party GenICam compliant SDKs allowing for upgrading current systems without changing application software. Teledyne DALSA Genie™ Nano 10GigE Cameras support the Trigger-to-Image Reliability (T2IR) framework which is a combination of hardware and software features that work together at a system level to help improve the reliability and reduce the downtime of imaging systems. These cameras are ideal for applications involving Electronics Manufacturing Inspection, Intelligent Traffic Systems, and Aerial Imaging.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.