

Cable length 1m; M16 12-pin plug (female), flying leads



LUMMAX® SWIR Area Lights

Stock **#90-877** NEW **2 In Stock**

MRP ₹6,903

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | ₹6,903 each |
| Need More? | Request Quote |

Product Downloads

General

115.0000.01 **Model Number:**

Note:
Compatible with LUMMAX® SWIR Area Lights (PID)
& Configurable Ring Lights (PID)

LUMMAX® **Manufacturer:**

Physical & Mechanical Properties

Length (m):

1

Weight (g):

61

Hardware & Interface Connectivity

Connector:

M16 12-pin plug (female) & flying leads

Input Voltage (V):

19 - 30 VDC

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- SWIR Wavelengths Options from 980 – 1600nm
- Compact 40 x 40mm Form Factor
- IP64 Rated for Dust and Moisture Protection

LUMIMAX® SWIR Area Lights provide powerful short-wave infrared (SWIR) illumination for demanding machine vision and inspection applications. Designed for wavelengths ranging from 980nm to 1600nm, these compact 40 x 40mm LED area lights deliver uniform, high-intensity output optimized for material sorting, semiconductor inspection, and moisture detection. An optional LUMIMAX Control Box (#90-883) simplifies power management and brightness adjustment, ensuring stable and consistent illumination performance. LUMIMAX® SWIR Area Lights feature industrial-grade construction, versatile mounting options, and can be used as spot, area, or backlight illuminators. These lights are ideal for applications requiring enhanced material contrast beyond the visible spectrum, and they provide reliable illumination for automation, quality control, and research environments.

;