

Coherent® Lasercam™ 33-6859-000 | UV Continuously Variable Attenuator

See More by [Coherent®](#)



Stock #12-419 [CONTACT US](#)

- 1 + MRP ₹4,24,800

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹4,24,800 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Active Area Diameter (mm):
15

Optical Properties

Maximum Incident Energy Density (mJ/cm²):
8

Wavelength Range (nm):
190 - 1100

Min. to Max. Attenuation:
10000000:1 to 3000:1

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 224:**

View **Certificate of Conformance:**

Country of Origin:
United States


Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 12 and 14-bit Digital USB 2.0 Interface Options
- High Sensitivity and Dynamic Range
- Intuitive BeamView™ Software Included

The Coherent® Lasercam™ Beam Profiler features excellent signal-to-noise ratio and linear response for accurate pulsed as well as CW laser beam dimension and uniformity measurements. The new BeamView™ 4.4 interface software features TCP/IP control and NI LabVIEW™ library suite, enabling efficient and smooth integration of beam profiling into any application. Examples of analysis functions that can be performed on the acquired beam images include: beam centroid location, beam peak intensity position, pointing stability, total relative power/energy in beam, peak power/energy density of beam, beam divergence, ellipticity, beam intensity uniformity, Gaussian fit, beam diameter/width based on second moments or user selectable percentage of peak/total energy.

Technical Information



Intuitive Software Interface

