

Cyan M34 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-708 10 TO 12 DAYS

⊖ 1 ⊕ **₹12,615**

ADD TO CART

Qty 1-9

₹12,615

Qty 10+

₹12,032

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-450, 600-1018

Clear Aperture CA (mm):
29.00

Coating:
Hard Coated

Filter Thread:
M34 x 0.50

Color:
Cyan

Center Wavelength CWL (nm):
505.00

Construction:
Mounted in Black Anodized Ring

Full Width-Half Max FWHM (nm):
90.00

Mount Thickness (mm):
5.2

Mount Thickness Including Threads (mm):
7.0

Outer Diameter (mm):
36.00

Substrate Thickness (mm):
1.3

Type:
Mounted Imaging Filter

Minimum Transmission (%):
≥85

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)
