

[See all 12 Products in Family](#)

TECHSPEC® 40mm Sq, 10kg Load Capacity, 14mm Travel, English Dovetail Stage



#16-712: Dovetail Stage, 40mm SQ, English



Stock **#16-712** **7 In Stock**

1 MRP ₹16,042

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹16,042 each
Qty 10+	₹14,175 each
Need More?	Request Quote

Product Downloads

General

Type: English

Included Hardware:
4X6-32, 5/16"L Socket Head Cap Screws; 1X3mm Allen Wrench; 1X2.5mm Allen Wrench

Physical & Mechanical Properties

Linear (X)	Type of Movement:
Dovetail	Guide System:
Center Drive	Drive Orientation:
40 x 40	Stage Size (mm):
14	Travel (mm):
0.55	Travel (inches):
Matte Black Finish Brass	Construction:
0.5	Leadscrew Pitch (mm):
10	Load Capacity (kg):
1.57 x 1.57	Stage Size (inches):
10	Straight Line Accuracy (µm):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	-----------------------

Threading & Mounting

(1) 1/4-20, (4) 6-32, (8) 2-56	Mounting Threads:
--------------------------------	--------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Compact Overall Size for System Integration
- Brass Construction for High Stiffness and up to 15kg Load Capacity
- Compatible with All TECHSPEC® Stages

TECHSPEC® High Load Capacity Dovetail Stages are a compact, cost-effective solution for linear adjustment within an optical system. These stages feature high stiffness brass construction and a hex driven movement, allowing for a low profile and compact overall size with 5, 10, and 15kg high load capacity options. The absence of tension springs and the included external plate lock ensure resistance to vibration and increase stability. TECHSPEC High Load Capacity Dovetail Stages are ideal for imaging and laser optics systems that require low profile integrated linear adjustments in demanding environments. These stages feature bolt patterns that are compatible with all TECHSPEC and comparable metric and English stages.

Technical Information



