

Dual Axis Linear Scale Micrometer



Stock **#58-608** 1 In Stock

-

1

+

₹52,200

ADD TO CART

Volume Pricing	
Qty 1-4	₹52,200 each
Qty 5+	₹49,626 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
No	NIST Certification:
Physical & Mechanical Properties	
	Scale Divisions:

Metric: 25µm English: 1 mil (0.001")	
25.4 x 76.2	Dimensions (mm):
1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):
Optical Properties	
Chrome on Glass	Substrate:
60-40	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

TECHNICAL INFORMATION

