

[See all 18 Products in Family](#)

DR-U3-50Y2M-C1-CS, Dragonfly S®, Rear USB, Full Housing CS, Mono Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Dragonfly® S



Stock **#70-341** **1 In Stock**

-

1

+

 ₹20,224

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹20,224 each
Need More?	Request Quote

Product Downloads

General	
Monochrome Camera	Type:
DR-U3-50Y2M-C1-CS	Model Number:
Teledyne FLIR	Manufacturer:

Dragonfly®	Camera Series:
Physical & Mechanical Properties	
Full	Housing:
Sensor	
96MB	Image Buffer:
1/2.5"	Sensor Format:
5.00	Resolution (Megapixels):
49.00	Frame Rate (fps):
2,592 x 1,944	Pixels (H x V):
2.2 x 2.2	Pixel Size, H x V (µm):
Rolling	Shutter Type:
10/12 bit	Pixel Depth:
9 µs to 0.5 seconds	Exposure Time:
USB3 Vision v1.0	Machine Vision Standard:
Electrical	
2.4 W maximum	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1 Micro B	Interface:
USB 3.1 Micro B	Connector:
Back Panel	Interface Port Orientation:
5 V via USB3 interface	Power Requirement:
Threading & Mounting	
CS-Mount	Mount:
Environmental & Durability Factors	
0°C to 50°C	Operating Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 240:
Canada	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ultra Compact Form Factor with Modular Design
- 5.0 Megapixel rolling shutter CMOS sensor
- Software and Hardware (rising or falling) triggering
- Low Power Consumption



Capture the exact images you need with advanced sensors and powerful features for volume based projects, at-scale manufacturing and multi-camera systems designed for volume based applications.

The **Dragonfly® S** has a modular design that makes it suitable to a wide range of applications and the price to performance ratio is unmatched. It is versatile, reliable, and practical. The compact lightweight design makes it ideal for deployment in small spaces or as a handheld device. Configured with a locking USB connector either on the rear or on the side and available either as a board level product or enclosed in an aluminum case. The 5.0 Megapixel rolling shutter CMOS sensor has a 1/2.5” frame format providing up to 49 FPS at full resolution (2592 x 1944).

The **Dragonfly® S** camera provides hardware and software triggered image capture, and also offers high-quality video streaming, for versatile deployment across a broad spectrum of applications in factory automation, life sciences and embedded devices. The large onboard memory ensures every captured image frame is transferred to the host without any loss, in a single or multi-camera setup.

Features

- Ultra-compact form factor
- Low power consumption
- Modular design
- Enclosed models hold Class B EMC safety compliance for healthcare or home use
- Spot and partial auto exposure modes
- Serial Communication
- Additive Binning
- Gain, White Balance, Black Level, EV compensation
- Software / Hardware (rising or falling) triggering
- Logic Blocks, Counters
- Color Correction

Applications

- Hand Held devices
- Medical systems
- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection