

[See all 36 Products in Family](#)

Dual Bandpass Green-NIR Filter M22.5



Stock #74-544 NEW **1 In Stock**

MRP ₹24,315

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹24,315 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):
40nm, 50nm ±5 nm

General

Type:
Dual Bandpass Mounted Imaging Filter

Model Number:
DB550/850-22.5

Physical & Mechanical Properties

Outer Diameter (mm):
24

Substrate Thickness (mm):

2mm

Optical Properties**Color:**

Green-NIR

Surface Quality:

40/20

Transmission (%):

≥85%

Transmission Wavelength (nm):

535-565nm, 830-870nm

Threading & Mounting**Filter Thread:**

M22.5 x 0.50

Mount Thickness (mm):

5.2

Regulatory Compliance**Certificate of Conformance:**[View](#)**Country of Origin:**

United States

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- Block and Transmit Desired Key MS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (MS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.