

Dual Bandpass VIS-940nm NIR filter M30.5



Stock **#74-584** NEW CONTACT US

-

1

+

₹10,179

ADD TO CART

Volume Pricing	
Qty 1+	₹10,179 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):

250nm, 50nm ±20 nm VIS, ±10 nm NIR

General	
Dual Bandpass Mounted Imaging Filter	Type:
DB940-30.5	Model Number:

Physical & Mechanical Properties	
32.5	Outer Diameter (mm):
	Substrate Thickness (mm):

1mm	
Optical Properties	
Color:	VIS-940nm-NIR
Surface Quality:	40/20
Transmission (%):	≥90%
Transmission Wavelength (nm):	405-650nm, 925-965nm
Threading & Mounting	
Filter Thread:	M30.5 x 0.50
Mount Thickness (mm):	5.2
Regulatory Compliance	
Certificate of Conformance:	View
Country of Origin:	United States
Imported By:	Edmund Optics India Private Limited

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.