

[See all 36 Products in Family](#)

Dual Bandpass Green-NIR Filter M30.5



Stock #74-548 NEW 1 In Stock

₹19,401

ADD TO CART

Volume Pricing

Qty 1+	₹19,401 each
Need More?	Request Quote

Product Downloads

Full Width-Half Max FWHM Range (nm):
40nm, 50nm ±5 nm

General

Dual Bandpass Mounted Imaging Filter **Type:**

DB550/850-30.5 **Model Number:**

Physical & Mechanical Properties

32.5 **Outer Diameter (mm):**

Substrate Thickness (mm):

2mm

Optical Properties

Green-NIR **Color:**

40/20 **Surface Quality:**

≥85% **Transmission (%):**

535-565nm, 830-870nm **Transmission Wavelength (nm):**

Threading & Mounting

M30.5 x 0.50 **Filter Thread:**

5.2 **Mount Thickness (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.